

BGBL1/ORK

by Burndy
Catalog ID: BGBL1/ORK

Prop 65 Notice

High Strength AL6061-T6 Aluminum Lay-In Lug, Voltage Rating: 600 V, Bolt Size: 3/8-24, Conductor Range (Main/Primary): 14 - 4 AWG.

Features: The Lay-In QIKLUG, Type BGBL Is Manufactured From High Strength 6061-T6 Aluminum, And Is Ideally Suited For Grounding And Bonding Applications Accommodating Both Copper And Aluminum Conductor Sizes #14 AWG To 250 KCMIL, UL486B Listed, AL9CU Rated, For Copper And Aluminum Conductor Combinations Up To 90 DEG C, 600 V Applications, UL Recognized For Grounding And Bonding. Ensures Reliability, Electro-Tin Plated, Provides Low Contact Resistance, Lay-In Feature, Eases Installation, Dimension T: 0.19 IN, Set Screw Type: Slot, Dimension N: 0.44 IN, Length: 1.63 IN, Height: 1.16 IN, Width: 0.63 IN Pad, Thickness: 0.19 IN, Conductor Type: Copper, Aluminium, Dimension D: 0.8 IN, Package: Clamshell



Product Details

General

| | |
|--------------|--|
| Application | For Grounding And Bonding Applications |
| Sub Brand | QIKLUG |
| Trade Name | QIKLUG™ |
| Type | BGBL |
| UPC | 781810359631 |
| UPC 12 Digit | 7818103596311 |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------------|---|
| Minimum Pack Quantity | 1 |
| Number of Pieces in Package | 2 |

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)