



## BIBS2/03FX

by Burndy  
Catalog ID: BIBS2/03FX

Prop 65 Notice

UNITAP, Single Sided Entry, #14-#4 Class B & C ,#14-#6 Class G,H,I,K, DLO, Aluminum.

Features: Clear Plastisol covered AL6061-T6 aluminum body, Saves time, lowers installation costs, eliminates taping, Oxide inhibitor pre-installed, Inhibits moisture and contaminants from entering the contact area

## Product Details

### General

Application	Tap connections and in-line splice/reductions are made quickly and easily with the UNITAP™ line of connectors
Color Code	Black
Insulation	Y
Material	Aluminum
Number Of Ports	3
Plated	Y
Plating Type	Tin
Sub Brand	UNITAP
Temperature Rating	-40° C to 135 °C
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC	621945439313
UPC 12 Digit	6219454393133

### Dimensions

Dimension - Length Overall inch	1.938 in
---------------------------------	----------

### Electrical Ratings

Amperage Rating	175 A
Rating - Minimum Voltage	600

### Conductor Related

Conductor - AL Str Size Range	1 AWG-14 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)