



BISR1/ORK

by Burndy
Catalog ID: BISR1/ORK

Prop 65 Notice

AL6061-T6 Aluminum Body Multi Tap Connector, UNITAP, Aluminum Conductor - Size Range: 8 AWG-1/0 AWG, Wire Strip Length: 1 IN.

Features: Clear Plastics Covered AL6061-T6 Aluminum Body: Saves Time, Lowers Installation Costs, Eliminates Taping, Clear Plastics: Allows Visual Confirmation That Conductor Is Properly Inserted, Oxide Inhibitor Pre-Installed: Inhibits Moisture And Contaminants From Entering The Contact Area, Range-Taking: Reduces Number Of Connectors Carried In Inventory, UL486B Listed, Dual-Rated AL9CU For Any Stranded Copper Or Stranded Aluminum Applications, 600 Volt, 90 DEG C, Wire Entry: In-Line, Torque: 50 IN-LB, Hex Size (key): 3/16 IN, Conductor Size (run - Range): 14 - 1/0 AWG, Wire Strip Length: 1 IN, Number Of Ports: 2, Type Of Insulation: Plastics

Product Details

General

Action	Contact Block
Application	For Indoor Use Only, Copper Or Stranded Aluminum For use with G Series custom control panel operators.
Material	Aluminum
Number Of Poles	1
Number Of Ports	2
Plated	N
Series	GO
Type	Contact Block BISR, POS
UPC	783936081199
UPC 12 Digit	7818103616100

Dimensions

Dimension - L Length Overall mm	74 mm
Dimension - Width inch	0.91 in
Gross Weight with Packaging	0.1
Height	1.75 in
Length	2 in
Width	1.75 in

Electrical Ratings

Amperage Rating	10 A
Contact Rating	10A @ 600 VAC
Frequency Rating	50/60 Hz

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Size Range	14 - 1/0 Str

Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size Range	14 -- 1/0 Str
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
Number of Pieces in Package	1

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)