



BITO2/0

by Burndy
Catalog ID: BITO2/0

Prop 65 Notice

Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 2 Sided Entry, 14-2/0 AWG, Al/Cu Rated, 1.52 L, 1.38 H.

Features: Clear Plastics Covered AL6061-T6 Aluminum Body: Saves Time, Lowers Installation Costs, Eliminates Taping, Clear Plastics: Allows Visual Confirmation That Conductor Is Properly Inserted, Oxide Inhibitor Pre-Installed: Inhibits Moisture And Contaminants From Entering The Contact Area, Range-Taking: Reduces Number Of Connectors Carried In Inventory, Wire Entry: Double, Torque: 120 IN-LB, Hex Size (key): 3/16 IN, Conductor Size (run - Range): 14 - 2/0 AWG, Number Of Ports: 2, Wire Strip Length: 11/16 IN, Type Of Insulation: Plastics

Product Details

General

Application	For Indoor Use Only, Copper Or Stranded Aluminum
Hex Key	3/16
Insulation	Y
Insulation Type	Plastics
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	90°C
Trade Name	UNITAP™
Type	BIT
UPC	781810133552
UPC 12 Digit	7818101335522

Dimensions

Dimension - Height inch	2.13 in
Dimension - L Length Overall mm	52.00 mm
Dimension - Length Overall inch	2.03 in
Dimension - Width inch	2.64 in
Dimension - Width mm	67.00 mm

Electrical Ratings

Operating Voltage	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size Range	14 str.- 2/0 str.
Conductor - Copper Str Size Range	14 str.- 2/0 str.
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)