


BTCGC1/OSS

by Burndy
Catalog ID: BTCGC1/OSS

Aluminum ground tray clamp, accomodates ground wire size #12 to 1/0 Kcmil



- Tin plated aluminum for durable, long lasting corrosion resistance
- cULus 467 Listed for Grounding and Bonding in US and Canada
- cULus 2703 Listed for solar PV applications in US and Canada
- Accommodates most popular styles of cable tray with inside or outside flange
- Quick and easy installation
- no drilling or special tools required
- Set screw bonds clamp to the cable tray while another set screw securely fastens the grounding conductor to the clamp providing vibration resistance and outstanding pull-out values
- Grounding green hardware as required in Section 8.4 of UL2703

Product Details

General

Application	Type BTCGC-SS clamps are suitable for outdoor applications and may be used with most types of cable tray with an inside or outside flange design
Finish Type	Tin Plated
Hex Size	9/16 in
Material	Aluminum
Material - Hardware	Stainless steel
UPC	621945546486

Dimensions

Height	1.55 in
Length	1.60 in
Thickness - Flange Plate	3/8 in
Width	0.75 in

Conductor Related

Conductor - AL Str Size Range	12 AWG - 1/0 Kcmil
Conductor - Copper Str Size Range	12 AWG - 1/0 Kcmil
Conductor Range	12 AWG - 1/0 Kcmil AL-CU

Certifications and Compliance

Certified Listed	cULus Listed
------------------	--------------

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)