



## BTCGC250SS

by Burndy  
Catalog ID: BTCGC250SS

Aluminum ground tray clamp, accomodates ground wire size #6 to 250 Kcmil

- Tin plated aluminum for durable, long lasting corrosion resistance
- cULus 467 Listed for Grounding and Bonding in US and Canada
- cULus 2703 Listed for solar PV applications in US and Canada
- Accommodates most popular styles of cable tray with inside or outside flange
- Quick and easy installation
- no drilling or special tools required
- Set screw bonds clamp to the cable tray while another set screw securely fastens the grounding conductor to the clamp providing vibration resistance and outstanding pull-out values
- Grounding green hardware as required in Section 8.4 of UL2703

## Product Details

### General

Allen Key Size	1/4 in
Application	Type BTCGC-SS clamps are suitable for outdoor applications and may be used with most types of cable tray with an inside or outside flange design
Finish Type	Tin Plated
Material	Aluminum
Material - Hardware	Stainless steel
UPC	621945505957

### Dimensions

Height	2.43 in
Length	2.25 in
Thickness - Flange Plate	1/2 in
Width	0.88 in

### Conductor Related

Conductor - AL Str Size Range	#6 AWG - 250 Kcmil
Conductor - Copper Str Size Range	#6 AWG - 250 Kcmil
Conductor Range	#6 AWG - 250 Kcmil AL-CU

### Certifications and Compliance

Certified Listed	cULus Listed
------------------	--------------

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)

