



C11HD4/ODB

by Burndy
Catalog ID: C11HD4/ODB

Prop 65 Notice

Cast Bronze Grnd Clamps, Water Pipe/Rebar/Grnd Rod -Grnd, Water Pipe- 1/2"-1" (13 -25) (Run), Rebar- #4 -#6 (Run)Grnd Rod -3/8"-1" (Run), Water Pipe- 1/2 " - 1 "(13 -25) (Run), Rebar #4-#6 (Run), Grnd Rod -3/8" - 1" (Run), Grnd-#8 - 4/0 (Tap).

Features: For Connecting Grounding Conductor, EMT Or Rigid Conduit To Water Pipe, Copper Tube, Ground Rod Or Rebar, Hub Swings 360 DEG For Easy Alignment, Simply Reverse Bottom Clamp For Smaller Size Rebar Or Rod, Connectors Are Provided With Silicon Bronze Hardware, Ground Rod Size: 3/8 - 1 IN Outer-Diameter, Rebar Size: #4 - #6, Installation Torque: 50 IN-LB For Screw, Water Pipe Size: 1/2 - 1 IN, Length: 2.65 IN, Width: 1.65 IN, Height: 2.25 IN

Product Details

General

Application	For Connecting Grounding Conductor, EMT Or Rigid Conduit To Water Pipe, Copper Tube, Ground Rod Or Rebar, Direct Burial Applications
Installation Torque Recommended in-lb	50 LBS/in
Material	Bronze Alloy
Material - Hardware	Zinc Plated Steel
Plated	N
Plating Type	Zinc
Sub Brand	CLAMP
Type	Ground Clamp
UPC	781810347751
UPC 12 Digit	7818103477511

Dimensions

Dimension - Height fraction	2.888888888888889 in
Dimension - Height inch	2.25 in
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.65 in
Dimension - Width fraction	1-14/25 in
Dimension - Width inch	1.56 in
Dimension - Width mm	40 mm

Conductor Related

Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	8 AWG-4/0 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 -1
Conductor - Rebar Size	4 ;5 ;6

Conductor - Rebar Size Range	4 -6
Conductor - Rod Size	3/8 in;1/2 in;5/8 in;3/4 in;7/8 in;1 in
Conductor - Rod Size Range	3/8 in-1 in

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)