



GCRT1/0

by Burndy
Catalog ID: GCRT1/0

Prop 65 Notice

Cast Copper Alloy Ground Clamp Range Taking, Up to 1/0, #8-1/0 AWG.

Features: Range taking design helps reduce inventory, UL and CSA listed, UL467 Listed for direct burial in earth and concrete

Product Details

General

Application	The GCRT1/0 works on 1/2 IN, 5/8 IN and 3/4 ground rods with a wire range of #8 through 1/0!
Material	Copper Alloy, Cast
Sub Brand	MECHANICAL CONNECTOR
Type	GCRT, Ground Connectors
UPC	781810451205
UPC 12 Digit	7818104512055

Dimensions

Dimension - Ground Rod Size	1/2"-3/4"
-----------------------------	-----------

Conductor Related

Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size Range	8 AWG-1/0
Conductor - Rod Size	1/2 in;5/8 in;3/4 in
Conductor - Rod Size Range	1/2 in-3/4 in

Certifications and Compliance

Certification - UL Listed Direct Burial	Yes
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	250 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)