



Oh No!
IMAGE COMING SOON

KAPO250R

by Burndy
Catalog ID: KAPO250R

Wire range: 2 -250 kcmil, Torque: 180-300 N lb.

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- Rated for use with Fine Strand Conductor
- 600 Volt Rated
- Range Taking conductor port
- Plastisol insulated covers provided with each connector

Product Details

General

Application	Terminate "upsized" conductor and/or fine strand conductor into mechanical connectors found in molded case circuit breakers, panel board equipment, and other switchgear.
Type	<ul style="list-style-type: none"> • 2 -250 kcmil Mechanical Pin Adaptor • Off-Centered Pin
UPC	621945554153

Dimensions

Height	1.81 in
Length	2.47 in
Outside Diameter	1.25
Width	1.43 in

Electrical Ratings

Amperage Rating	290
Voltage Rating	600 V

Conductor Related

Conductor - AL Str Size Range	#2 -250 kcmil
Conductor - Copper DLO Size Range	#2 -250 kcmil
Conductor - Copper Flex H Size Range	#2 -250 kcmil
Conductor - Copper Flex I Size Range	#2 -250 kcmil
Conductor - Copper Flex K Size Range	#2 -250 kcmil
Conductor - Copper Str Run	#2 -250 kcmil
Conductor - Copper Str Size Range	#2 -250 kcmil