



KS15RK

by Burndy
Catalog ID: KS15RK

Prop 65 Notice

High copper alloy Split Bolt, SERVIT, Torque: 165 in-lb, Copper Conductor Stranded - Run Range: 8 Str. - 6 Sol.

Features: UL467 Listed For Direct Burial Applications In Earth Or Concrete, Compact, High-Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Cracking And Corrosion, Width: 0.38 IN, Conductor Type: Run And Tap: Solid Copperweld, Commercial Stranded And Solid Copper, Length: 0.45 IN, Installation Torque: 80 IN-LB, Package: Clamshell, Cross Flats: 0.5 IN

Product Details

General

Application	For Direct Burial Applications In Earth Or Concrete, Copper
Connector Type	Split Bolt
Construction Material - Main	Copper
Installation Torque Recommended in-lb	80 LBS/in
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT
Type	KS, Compact
UPC	781810359983
UPC 12 Digit	7818103599833

Dimensions

Dimension - B Length fraction	9/20 in
Dimension - B Length inch	0.45 in
Dimension - Cross Flats inch	0.5 in
Dimension - Length Overall inch	0.85 in
Dimension - Thread Size	-
Dimension - Width fraction	53/93 in
Dimension - Width inch	0.57 in

Conductor Related

Conductor - Copper Str Run	10 AWG;9 AWG;8 AWG
Conductor - Copper Str Run Range	10 AWG-8 AWG
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Tap Range	14 AWG-8 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	N
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
Number of Pieces in Package	5
Packaging Type	Clamshell

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)