



KS17RK

by Burndy
Catalog ID: KS17RK

Prop 65 Notice

High copper alloy Split Bolt, SERVIT, Torque: 80 in-lb, Copper Conductor Solid - Tap Range: 14 AWG-8 AWG.

Features: UL467 Listed For Direct Burial Applications In Earth Or Concrete, Compact, High-Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Cracking And Corrosion, Width: 0.45 IN, Package: Clamshell, Cross Flats: 0.63 IN, Installation Torque: 165 IN-LB, Length: 1.14 IN, Conductor Type: Run And Tap: Solid Copperweld, Commercial Stranded And Solid Copper, Type D Copperweld, Stranded Copperweld, Type A Copperweld

Product Details

General

| | |
|---------------------------------------|---|
| Application | For Direct Burial Applications In Earth Or Concrete, Copper |
| Connector Type | Split Bolt |
| Construction Material - Main | Copper |
| Installation Torque Recommended in-lb | 165 LBS/in |
| Material | Copper |
| Plated | N |
| Plating Type | Unplated |
| Sub Brand | SERVIT |
| Trade Name | SERVIT |
| Type | KS, Compact |
| UPC | 781810360002 |
| UPC 12 Digit | 7818103600022 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - B Length fraction | 29/50 in |
| Dimension - B Length inch | 0.58 in |
| Dimension - Cross Flats inch | 0.63 in |
| Dimension - Length Overall inch | 1.14 in |
| Dimension - Thread Size | - |
| Dimension - Width fraction | 7/10 in |
| Dimension - Width inch | 0.7 in |

Conductor Related

| | |
|------------------------------------|--|
| Conductor - Copper Solid Run | 9 AWG; 8 AWG; 7 AWG; 6 AWG |
| Conductor - Copper Solid Run Range | 9 AWG-6 AWG |
| Conductor - Copper Solid Tap | 14 AWG; 13 AWG; 12 AWG; 11 AWG; 10 AWG; 9 AWG; 8 AWG; 7 AWG; 6 AWG |
| Conductor - Copper Solid Tap Range | 14 AWG-6 AWG |
| Conductor - Copper Str Run | 8 AWG |

| | |
|----------------------------------|----------------------------------|
| Conductor - Copper Str Run Range | 8 AWG |
| Conductor - Copper Str Tap | 14 AWG;12 AWG;10 AWG;9 AWG;8 AWG |
| Conductor - Copper Str Tap Range | 14 AWG-8 AWG |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------------|-----------|
| Minimum Pack Quantity | 10 |
| Number of Pieces in Package | 3 |
| Packaging Type | Clamshell |

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)