



KS20RK

by Burndy
Catalog ID: KS20RK

Prop 65 Notice

High copper alloy Split Bolt, SERVIT, Torque: 165 in-lb.

Features: UL467 Listed For Direct Burial Applications In Earth Or Concrete, Compact, High-Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Cracking And Corrosion, Length: 1.2 IN, Conductor Type: Run And Tap: Solid Copperweld, Commercial Stranded And Solid Copper, Type D Copperweld, Stranded Copperweld, Type A Copperweld, Width: 0.51 IN, Cross Flats: 0.69 IN, Package: Clamshell

Product Details

General

Application	For Direct Burial Applications In Earth Or Concrete, Copper
Connector Type	Split Bolt
Construction Material - Main	Copper
Installation Torque Recommended in-lb	165 LBS/in
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT
Type	KS, Compact
UPC	781810360019
UPC 12 Digit	7818103600199

Dimensions

Dimension - B Length fraction	13/20 in
Dimension - B Length inch	0.65 in
Dimension - Cross Flats inch	0.64 in
Dimension - Length Overall inch	1.2 in
Dimension - Thread Size	-
Dimension - Width fraction	39/50 in
Dimension - Width inch	0.78 in

Conductor Related

Conductor - Copper Solid Run	9;8;7;6;5;4
Conductor - Copper Solid Tap	14;13;12;11;10;9;8;7;6;5;4
Conductor - Copper Str Run	8;7;6
Conductor - Copper Str Tap	14;12;10;9;8;7;6

Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
Number of Pieces in Package	3
Packaging Type	Clamshell

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)