

# PAT444SL5PB

by Burndy  
Catalog ID: PAT444SL5PB

Prop 65 Notice

PATRIOT 11-Ton C-Head Dieless Tool, 5.0Ah 18V Li-ion, 120V-AC Charger, Nylon Pro Bag

- C-Head, Dieless system with range taking capability
- #4 -1000 kcmil Cu & Al, #4 - 556.6 ACSR, ACAR, AAC, AAAC
- 355° Head Rotation

C-Head, Dieless System with Range Taking Capability  
5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime warranty on INFINITY DRIVE®



## Product Details

### General

Application	Crimping
Battery Type	Accepts 2Ah-6Ah Makita Lithium-Ion
Crimp Force Capacity	11 ton
Die Type	Dieless
Sub Brand	PATRIOT® Crimper
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945561786
UPC 12 Digit	621945561786

### Dimensions

Height	16.9 in
Length	3.2 in
Width	13.7 in

### Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

### Conductor Related

Crimping Ranges	Copper: #4 AWG - 1000 Kcmil; Aluminum: 4-1000 Kcmil; ACSR: #4 AWG-556.6 Kcmil
-----------------	---

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)