

PAT444SLCBPB

by Burndy
Catalog ID: PAT444SLCBPB

Prop 65 Notice

PATRIOT 11-Ton C-Head Dieless Tool, No Battery/Charger, Nylon Pro Bag

- C-Head, Dieless system with range taking capability
- #4 -1000 kcmil Cu & Al,#4 - 556.6 ACSR, ACAR, AAC, AAAC
- 355° Head Rotation
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Durable high impact formed carrying case provides superior protection and stores all accessories 5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime warranty on INFINITY DRIVE®



Product Details

General

Application	Crimping
Battery Type	Accepts 2Ah-6Ah Makita Lithium-Ion
Crimp Force Capacity	11 ton
Die Type	Dieless
Sub Brand	PATRIOT® Crimper
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945561793
UPC 12 Digit	621945561793

Dimensions

Height	16.9 in
Length	3.2 in
Width	13.7 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #4 AWG - 1000 Kcmil; Aluminum: 4-1000 Kcmil; ACSR: #4 AWG-556.6 Kcmil
-----------------	---

Certifications and Compliance

Certification - ETL	No
---------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)