

PAT46CLWSLILCBPB

by Burndy
Catalog ID: PAT46CLWSLILCBPB

Prop 65 Notice

PATRIOT 15-Ton Covered C-Head Tool, No Battery/Charger, Nylon Pro Bag

5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime warranty on INFINITY DRIVE®



Product Details

General

Application	Crimping
Battery Type	Accepts 2Ah-6Ah Makita Lithium-Ion
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
Sub Brand	PATRIOT® Crimper
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945561687
UPC 12 Digit	621945561687

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #14 AWG - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil
-----------------	---

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)