

# PAT46LWLIPB

by Burndy  
Catalog ID: PAT46LWLIPB

Prop 65 Notice

PATRIOT 15-Ton Latch Head Tool, 3.0Ah 18V Li-ion, 120V-AC Charger, Nylon Pro Bag

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- Light weight, "latch head" with 355° head rotation
- Ergonomically balanced

Cu:#8 AWG str., 1500 kcmil, grounding: to 500 kcmil, YGA, YGHA, YGFTerminals, uninsul: #8 to1500 kcmil: YA, YA-2N, YA-L,YA-LB, YA-TC, YA-2LN,YAB-4N, YAV-L, ,YAV-RS, YA-TC-FX,Terminals, insul: #8 to 2/0,YAEV,Splices: #8 to 1500 kcmil,YS, YS-T, YS-L, YS-LB, YST,YSP-T, YGS, YGHS Taps:YH, YCHC #14 to 1000 kcmil,YC-C to 4/0 AWG,Taps, grounding: to 500 kcmilYGHC-C, YGHP-C, YGHR-C, Al #8 AWG -1250 kcmil YA-A, AYP, AYPO, Splices:YS-A, YS-AT, YRB, Taps:YFD, YFN, YFO, YFR5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime warranty on INFINITY DRIVE®



## Product Details

### General

Application	Crimping
Battery Type	Accepts 2Ah-6Ah Makita Lithium-Ion
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
Recharge Time	0.5 h
Sub Brand	PATRIOT® Crimper
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945561472
UPC 12 Digit	621945561472

### Dimensions

Height	13.93 in
Jaw Width	2 in
Length	18.59 in
Weight	16.8 lb
Width	3.26 in

### Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

### Conductor Related

Crimping Ranges	Copper: #14 AWG - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil
-----------------	-------------------------------------------------------------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)