

PAT46LWSLIPB

by Burndy
Catalog ID: PAT46LWSLIPB

Prop 65 Notice

PATRIOT 15-Ton C-Head Tool, 3.0Ah 18V Li-ion, 120V-AC Charger, Nylon Pro Bag

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter
- Light weight, scoop style C-head with 355° head rotation
- Overmolded, ergonomic handle
- Improved ergonomic balance

2 in jaw opening, Used with P dies, U dies with PUADP-1 adapter (sold separately), Scoop style C-head with 355 DEG head rotation, Overmolded, ergonomic handle, Improved ergonomic balance, Includes 2 batteries, charger, and polymer carrying case 5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime warranty on INFINITY DRIVE®



Product Details

General

Application	Crimping
Battery Type	Accepts 2Ah-6Ah Makita Lithium-Ion
Crimp Force Capacity	15 ton
Die Type	P Die and U Die with PUADP1 Adapter
Recharge Time	0.5 h
Sub Brand	PATRIOT® Crimper
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945561632
UPC 12 Digit	621945561632

Dimensions

Height	12.88 in
Jaw Width	2.00 in
Length	18.44 in
Weight	18.9 lb
Width	3.26 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #14 AWG - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, (2) 3Ah 18V li-ion batteries, charger, lanyard and case

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)