

# PAT600CLIPB

by Burndy  
Catalog ID: PAT600CLIPB

Prop 65 Notice

PATRIOT 6-Ton Covered Latch Head Tool, 3.0Ah 18V Li-ion, 120V-AC Charger, Nylon Pro Bag

- Specialized latch head design
- Ergonomic design allows one hand operation for Ram advance and Ram retraction
- 180 degree head rotation
- Permanent D3 crimp groove accepts all W Dies
- Enhanced clearance for tap connections

5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime warranty on INFINITY DRIVE®



## Product Details

### General

Application	Crimping
Battery Type	Accepts 2Ah-6Ah Makita Lithium-Ion
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
Recharge Time	0.5 h
Sub Brand	PATRIOT® Crimper
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimper
UPC	621945562233
UPC 12 Digit	621945562233

### Dimensions

Height	13.7 in
Length	14.5 in
Weight	10.1 lb
Width	3.5 in

### Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

### Conductor Related

Crimping Ranges	Copper: #8 AWG-600 Kcmil; Copper Flex: #8 AWG-350 Kcmil Flex; Aluminum: #8 AWG-350 Kcmil
-----------------	--

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)