



PAT750T3C03A2

by Burndy
Catalog ID: PAT750T3C03A2

Prop 65 Notice

PATRIOT® T3 Technology 12-Ton Battery Crimper, C-Head, Rubber Covered, two 3.0Ah 18V Li-Ion Batteries, 120V-AC Charger, Hard Case

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- C-head with 1.65" jaw opening with 355° head rotation; Used with U dies
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries

Product Details

General

Application	Crimping
Battery Type	Lithium-ion
Crimp Force Capacity	12 ton
Die Type	U Die
Sub Brand	PATRIOT®
Tool Type	Battery Actuated Crimper
Type	Crimper
UPC	621945558960
UPC 12 Digit	621945558960

Dimensions

Height	15.75 in
Jaw Width	1.65 in
Length	14.75 in
Weight	30.9 lb
Width	3.25 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Tension Sleeves: Copper #8 Sol-500 kcmil, Aluminum #8 Sol-587.2 kcmil, ACSR #4-556.5 kcmil; Taps: Copper #14 Sol-500 kcmil, Aluminum #8-500 kcmil; Aerial Cable Copper #6-500 kcmil; Terminals & Splices: Copper #8-750 kcmil, Aluminum #8-750 kcmil, ACSR #4-556.5 kcmil; HYGROUND®: Copper #8-500 kcmil, Ground Rods 1/2"-1" diameter
-----------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)