

PAT750T3U05D2

by Burndy
Catalog ID: PAT750T3U05D2

Prop 65 Notice

PATRIOT® T3 Technology 12-Ton Battery Crimper, C-Head, Uncovered, two 5.0Ah 18V Li-Ion Batteries, 12V-DC Charger, Hard Case

- TRACK crimp locations with onboard GPS - BURNDY Exclusive!
- TRACE individual crimps with comments and output force validation
- TRANSMIT via Bluetooth® technology and sync data to the cloud
- C-head with 1.65" jaw opening with 355° head rotation; Used with U dies
- Bright LED worklight and Red/Green LED to validate output force
- Improved ergonomic design with more balance and better grip to reduce user fatigue
- Patented T-Track alignment guide for HYGROUND® as well as other asymmetrical connectors
- Accepts 2.0Ah-6.0Ah Makita Lithium-ion Batteries



Product Details

General

| | |
|----------------------|--------------------------|
| Application | Crimping |
| Battery Type | Lithium-ion |
| Crimp Force Capacity | 12 ton |
| Die Type | U Die |
| Sub Brand | PATRIOT® |
| Tool Type | Battery Actuated Crimper |
| Type | Crimper |
| UPC | 621945559004 |
| UPC 12 Digit | 621945559004 |

Dimensions

| | |
|-----------|----------|
| Height | 15.75 in |
| Jaw Width | 1.65 in |
| Length | 14.75 in |
| Weight | 30.1 lb |
| Width | 3.25 in |

Electrical Ratings

| | |
|-------------------|--------|
| Operating Voltage | 18 VDC |
|-------------------|--------|

Conductor Related

| | |
|-----------------|---|
| Crimping Ranges | Tension Sleeves: Copper #8 Sol-500 kcmil, Aluminum #8 Sol-587.2 kcmil, ACSR #4-556.5 kcmil; Taps: Copper #14 Sol-500 kcmil, Aluminum #8-500 kcmil; Aerial Cable Copper #6-500 kcmil; Terminals & Splices: Copper #8-750 kcmil, Aluminum #8-750 kcmil, ACSR #4-556.5 kcmil; HYGROUND®: Copper #8-500 kcmil, Ground Rods 1/2"-1" diameter |
|-----------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)