

PATCUT1500LIPB

by Burndy
Catalog ID: PATCUT1500LIPB

Prop 65 Notice

PATRIOT 1500 Series CU/AL Cutter with Nylon Pro Bag, 3.0Ah Battery & Charger

- Variable speed trigger
- Forward/Reverse switch features a locking position
- Large, strategically placed, non-skid bumper
- LED Worklight
- EP Enhanced Power tools accept 2.0, 3.0, 4.0, 5.0, and 6.0Ah Makita batteries

Aluminum up to 1500 kcmil, Copper Flex up to 1250 kcmil, Copper (soft drawn) up to 1000 kcmil, Copper (hard drawn) up to 750 kcmil, [DO NOT CUT STEEL OR ACSR] 3 Year Limited Warranty on Tool, 3 Year on Batteries and Charger



Product Details

General

Application	Cutting
Battery Type	Accepts 2Ah-6Ah Makita Lithium-Ion
Recharge Time	0.5 h
Sub Brand	PATRIOT® Cutter
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutter
UPC	621945562394
UPC 12 Digit	621945562394

Dimensions

Height	15.5 in
Length	6 in
Width	4.38 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Cutting Capacity: Soft drawn copper: 1000 Kcmil; Aluminum: 1500 Kcmil
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
UL Listed	No

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, (1) 3Ah 18V li-ion battery, charger, lanyard and case

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)