



PATMD34003A3

by Burndy
Catalog ID: PATMD34003A3

Prop 65 Notice

IN-LINE® Tool, crimping jaw (O/D3 groove), ACSR cutting jaw, two (2) Makita 3.0Ah Batteries, 120V-AC Charger, Nylon Pro Bag

5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime warranty on INFINITY DRIVE®

Product Details

General

Application	Crimping & Cutting
Battery Type	Accepts 2Ah-6Ah Makita Lithium-Ion
Crimp Force Capacity	6 ton
Die Type	W Die and X Die
Recharge Time	0.5 h
Sub Brand	PATRIOT® IN-LINE® Crimp/Cut Kit
Tool Type	Battery Actuated Crimper & Cutter
Trade Name	PATRIOT®
Type	Crimper & Cutter
UPC	621945585720
UPC 12 Digit	621945585720

Dimensions

Height	2.75 in
Length	18.7 in
Weight	9.2 lb
Width	4.375 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Crimping Capacity: Copper: #8 AWG - 500 kcmil; Copper Flex: #8 AWG - 350 kcmil; AAC: #14 AWG - 350 kcmil; ACSR: #14 - 4/0 AWG; Cutting Capacity: ACSR: upto 556.5 kcmil (26/7)
-----------------	--

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)