

QP10F250D

by Burndy
Catalog ID: QP10F250D

Prop 65 Notice

MATERIAL: TIN-PLATED BRASS. 600 VOLTS MAX. 105 C MAX.



Product Details

General

Connector Type	Female Disconnect
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP
Type	Disconnect Connectors
UPC	781810020623
UPC 12 Digit	7818100206233

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - F Width Center to Center inch	0.11 in
Dimension - Length Overall inch	1.00 in
Dimension - Thread Size	-
Dimension - Width inch	0.29 in
Dimension - Width mm	7 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size Range	N/A
Conductor - Copper Str Size	16 AWG;14 AWG

Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	N
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	600 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)