

# RHCC2156ACSR

by Burndy  
Catalog ID: RHCC2156ACSR

Prop 65 Notice

Remote Operated, Latch Head Cuts up to 2156 kcmil ACSR

- 180° head rotation
- Durable hardened, precision steel blades
- Specialized latch head for mid-span cuts
- Durable canvas carrying bag stores tool and accessories



## Product Details

### General

Application	Cutting
Type	Cutters
UPC	781810671559
UPC 12 Digit	7818106715599

### Dimensions

Dimension - Thread Size	-
Height	4.13 in
Length	13.17 in
Weight	10 lb
Width	2.69 in

### Certifications and Compliance

Certification - ETL	No
Standards - RoHS Compliance Status	UI

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)