



Anchor, Disk, 20in X .187in fits 1in rod

by CHANCE Utility
Catalog ID: C1022011

Corrosion-Resistant Anchor .187" (4.7mm) Thick for 20" (508 mm) Hole used with 1" (25.4 mm) Diameter Rod.

- Designed to be used with Protected Anchor Rods, Fiber Washer and Cap Nut
- Coated with black paint



* Representative image

Product Details

General

Type	Corrosion-Resistant Anchor Parts
UPC	096359008538

Dimensions

Anchor Hole Size	20 in
Rod Diameter - Order Separately	1.000 in
Thickness	0.187 in
Weight	19.110 lb

Logistics

Pallet Quantity	40 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com