



Anchor, Tough One, 12in, 10,000 ft-lb rating, 2.5in hub, 5/8in threads

by CHANCE Utility
Catalog ID: C1025010

Tough One Anchor Helix, 10,000 Ft Lbs (10,848 N-M), 12" (304 mm) Helix for use with 0.625" (15.9 mm) Rod.

- Installed with Chance anchor wrench C3031064 or C3030983
- The anchor's sloped lead point improves penetration and helps soil flow from below the hub to above the anchor.
- 5/8" threads to fit 5/8" diameter Pisa rod
- Anchors are painted with a black paint



* Representative image

Product Details

General

Coating	Painted
Number of Helices	1
Torque Rating	10000 ft-lbs
Type	Anchor Helix
UPC	096359008750

Dimensions

Anchor Helix Diameter(s)	12 in
Anchor Hub Size	2.500 in
Rod Diameter	0.625 in
Weight	21.188 lb

Logistics

Pallet Quantity	72 EA
Standard Package	2

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com