



* Representative image

Anchor, Lead, SS175, 8/10 X 3.5ft

by CHANCE Utility
Catalog ID: C1100227

Square Shaft (SS 175) Lead Section, 30" (762 mm) long with 8" (203 mm) - 10" (254 mm) Helices.

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

Product Details

General

Coating	Galvanized
Number of Helices	2
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	100000 lb
Torque Rating	10500 ft-lbs
Type	Lead Sections
UPC	096359009696

Dimensions

Anchor Helix Diameter(s)	8 in - 10 in
Length	30.000 in
Weight	50.147 lb

Logistics

Pallet Quantity	12 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com