



* Representative image

Anchor, Lead, SS150, 8/10 X 3.5ft

by CHANCE Utility
Catalog ID: C1100385

Square Shaft (SS 150) Lead Section, 30" (762 mm) long with 8" (203 mm) - 10" (254 mm) Helices.

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

Product Details

General

Coating	Galvanized
Number of Helices	2
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb
Torque Rating	7000 ft-lbs
Type	Lead Sections
UPC	096359009726

Dimensions

Anchor Helix Diameter(s)	8 in - 10 in
Length	30.000 in
Weight	37.975 lb

Logistics

Pallet Quantity	12 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service
 Hubbell Power Systems
 210 N. Allen Centralia, MO 65240 USA
 Phone: (573) 682-5521
 Fax: (573) 682-8475
 Email: hpscsc@hubbell.com

International Customer Service
 Phone: +1-573-682-5521
 Fax: +1-573-682-8516
 Email: hpsintlcs@hubbell.com