



\* Representative image

# Anchor, Extension, SS175, 14 X 4ft

by CHANCE Utility  
Catalog ID: C1100472

Square Shaft (SS 175) Extension 48" long (1219 mm) w/ 14" (355 mm) Helix.

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

## Product Details

### General

Coating	Galvanized
Number of Helices	1
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	100000 lb
Torque Rating	10500 ft-lbs
Type	Anchor Extensions
UPC	096359009818

### Dimensions

Anchor Helix Diameter(s)	14 in
Length	48.000 in
Weight	67.865 lb

### Logistics

Pallet Quantity	20 EA
Standard Package	1

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com