



* Representative image

Anchor, Lead, SS150, 14/14/14 X 10ft

by CHANCE Utility
Catalog ID: C1100504

Square Shaft (SS 150) Lead Section, 120" (3048 mm) long with 14" (355 mm) - 14" (355 mm) -14" (355 mm) Helices.

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

Product Details

General

Coating	Galvanized
Number of Helices	3
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb
Torque Rating	7000 ft-lbs
Type	Lead Sections
UPC	096359009849

Dimensions

Anchor Helix Diameter(s)	14 in - 14 in - 14 in
Length	120.000 in
Weight	132.790 lb

Logistics

Pallet Quantity	12 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com