



\* Representative image

# Anchor, Lead, SS175, 14/14/14 X 10ft

by CHANCE Utility  
Catalog ID: C1100505

Square Shaft (SS 175) Lead Section, 120" (3048 mm) long with 14" (355 mm) - 14" (355 mm) -14" (355 mm) Helices.

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

## Product Details

### General

Coating	Galvanized, ASTM A-153
Number of Helices	3
Pipe Type	Square Bar
Style	Square Shaft (SS 175) Anchor
Torque Rating	10500 ft-lbs
Type	Lead Sections
UPC	096359009856

### Dimensions

Anchor Helix Diameter(s)	14 in - 14 in - 14 in
Foundation Diameter	1.750 in
Foundation Length	124 in
Weight	167 lb

### Logistics

Pallet Quantity	12 EA
Standard Package	1

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)