



* Representative image

2" Square Shaft Helical Extension(SS200), 14/14 x 7ft

by CHANCE Utility
Catalog ID: C1100581

SS200, 80" long with 14", 14" helices

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

Product Details

General

Coating	Galvanized
Number of Helices	2
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	150000 lb
Torque Rating	15000 ft-lbs
Type	Anchor Extensions
UPC	096359010036

Dimensions

Anchor Helix Diameter(s)	14 in - 14 in
Length	80.000 in
Weight	148.715 lb

Logistics

Pallet Quantity	12 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com