



* Representative image

2.25" Square Shaft Helical Extension(SS225), 14 x 3-1/2ft

by CHANCE Utility
Catalog ID: C1100650

SS225, 39" long with 14" helix

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

Product Details

General

Coating	Galvanized
Number of Helices	1
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	200000 lb
Torque Rating	21000 ft-lbs
Type	Anchor Extensions
UPC	096359010104

Dimensions

Anchor Helix Diameter(s)	14 in
Length	39.000 in
Weight	78.750 lb

Logistics

Pallet Quantity	12 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com