



\* Representative image

# Anchor, Lead, SS175, 10/12 X 5ft

by CHANCE Utility  
Catalog ID: C1100884

Square Shaft (SS 175) Lead Section 60" (1524 mm) long with 10" (254 mm) -12" (304 mm) Helices.

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

## Product Details

### General

Coating	Galvanized
Number of Helices	2
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	100000 lb
Torque Rating	10500 ft-lbs
Type	Lead Sections
UPC	096359489733

### Dimensions

Anchor Helix Diameter(s)	10 in - 12 in
Length	66.000 in
Weight	80.1 lb

### Logistics

Pallet Quantity	20 EA
Standard Package	1

For further technical assistance, please contact us

**Domestic Customer Service**  
 Hubbell Power Systems  
 210 N. Allen Centralia, MO 65240 USA  
 Phone: (573) 682-5521  
 Fax: (573) 682-8475  
 Email: hpscsc@hubbell.com

**International Customer Service**  
 Phone: +1-573-682-5521  
 Fax: +1-573-682-8516  
 Email: hpsintlcs@hubbell.com