



# Anchor, Tool, Kelly Bar Adapter, 2.5in Square, 15,000 ft-lb rating

by CHANCE Utility  
Catalog ID: C3030955

2.5" Square 15K Kelly bar Adapter.

- Kelly Bar Adapter attaches to truck's torque motor drive shaft (Kelly Bar)
- Kelly bar adapter has twelve holes for 5/8" bolts on a 75/8" bolt circle, comes with twelve 5/8" Grade 2 bolts, nuts & lockwashers and bent arm pin with coil lock
- Painted with green paint

## Product Details

### General

Bolt Grade	2
Kelly Bar Shape	Square
Number of Bolt Holes	12
Torque Rating	15000 ft-lbs
Type	Anchor/Pile Installation Tools
UPC	096359015321

### Dimensions

Anchor Installation Hole Size	0.625 in
Diameter - Bolt	0.625 in
Diameter - Bolt Circle	7.625 in
Kelly Bar Adapter Inside Width	2.5 in
Kelly Bar Hole Distance to Flange	2.25 in
Length	7.000 in
Weight	24.500 lb

### Logistics

Pallet Quantity	48 EA
Standard Package	1

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: hpscsc@hubbell.com

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: hpsintlcs@hubbell.com