



Spiral Link Stick, 57.5"

by CHANCE Utility
Catalog ID: C4000812

The Spiral Link Stick is used in lieu of a strain link stick in close places where the lineman cannot safely install a strain link stick by hand. A lifting eye on the head ferrule enables the lineman to guide the Spiral Link Stick to the conductor with a hotstick. The pole of the Spiral Link Stick is made of 11/4" Epoxiglas®. Ferrule castings are of heat-treated aluminum alloy- spiral hook and butt ring of galvanized steel.



Product Details

General

| | |
|-------|----------------------|
| Duty | 3,500 lbs. (1588 kg) |
| Style | Spiral Link Stick |
| UPC | 096359016830 |

Dimensions

| | |
|----------------------------|-----------|
| Length | 42 in |
| Length - Insulated Section | 42 in |
| Lengths - Extended | 57.5 |
| Weight | 10.094 lb |

Conductor Related

| | |
|-----------|-------------------|
| Wire Size | 1510.5 kcmil ACSR |
|-----------|-------------------|

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com