



Double and Triple Blocks with 150' of 1/2", 3-str. Polypropylene Rope

by CHANCE Utility
Catalog ID: C4000915

DOUBLE+TRIPLE BLOCKS-150FT 1/2IN PP ROPE, The shells and sheaves are made of high dielectric, fiberfilled natural nylon. The shaft is of silicon bronze and the sheave bearings are oil impregnated bronze. Blocks are available with either polypropylene or Poly-Dacron rope for minimum stretch and long service life. Dielectric Strength: Dielectric rating in dry weather is 30,000 volts between the bearing and the mounting bolt nut. Maximum 1/2" rope.

Product Details

General

Max Load Lbs.	3500 lb
Style	Double & Triple Blocks w/ 150' of Rope
Type	Load Lift Assist
UPC	096359016908

Dimensions

Weight	16.0 lb
--------	---------

Logistics

Pallet Quantity	24 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com