



Yoke, For Rect Or Tri Plates

by CHANCE Utility
Catalog ID: C4011717



* Representative image

YOKE, FOR RECT OR TRI PLATES, These yokes can be used with adjustable strain poles to remove the strain from one string of multiple strings of deadend insulators. Because the yokes are designed to fit various types of yoke plates, they should be purchased in pairs to fit the specific construction. The same yoke assemblies can be used on both the hot and cold end of the insulator string as they hook into the yoke plate hardware. All of these yokes are rated at 15,000 pounds maximum load per insulator string.

Product Details

General

Style	Single Pole Strain Carrier Yokes
UPC	096359017608

Dimensions

Maximum Distance Between Yokes	105
Minimum Distance Between Yokes	71.5
Weight	20.58 lb

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com