



Yoke, 2 Pole Hot End Assy

by CHANCE Utility
Catalog ID: C4011720

Two-pole yokes can be ordered separately to make up any of the two pole strain carriers. The yokes are fabricated of high strength (.75" and 1" thick) aluminum plate. The yokes have 26" width between the center of the adjustable strain poles used with them. Maximum load ratings are 15,000 pounds per insulator string.



Product Details

General

Style	Two Pole Strain Carrier - Accessories
UPC	096359017639

Dimensions

Weight	39.2 lb
--------	---------

Logistics

Pallet Quantity	10 EA
-----------------	-------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com