



# Insulated Ratchet Cable Cutter For 1000 kcmil A.A. / 500 kcmil Cu, 6'

by CHANCE Utility  
Catalog ID: C4031381

WIRECUTTER, RATCHET 6', High-performance design incorporates Delrin plastic rollers and a two-piece operating rod. Roller mechanism travels smoothly along main Epoxiglas® pole. Linked through the roller support unit, the hinged operating rod and larger Epoxiglas pole reinforce each other. These Ratchet Cable Cutters meet OSHA Electrical Rating subpart V-section 1926.951 (d). Insulated support pole is Chance orange 112"-diameter Epoxiglas with Plastisol butt cap, operating shaft is 38"-diameter solid fiberglass rod, and lever handle is 1"-diameter Epoxiglas with rubber cushion grip.



\* Representative image

## Product Details

### General

Storage Bag Included?	T306-0028 (Bag not included. Must be ordered separately.)
Type	Cutters
UPC	096359019046

### Dimensions

Length	72 in
Weight	9.8 lb

### Conductor Related

Conductor Size	1000 MCM A.A. / 500 MCM Cu.
----------------	-----------------------------

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)