



# Class 2, Short-Lip Flexible Line Hose, 3'

by CHANCE Utility  
Catalog ID: C4060294



LINE HOSE, 1 1/4"X36" STRAIGHT, Much lighter in weight than other flexible dielectric cover-up, Chance Line Hose helps protect workers from accidental contact with conductors. In accordance with ASTM D 1050-90, Chance ozone/corona resistant thermoplastic elastomer offers excellent performance properties. It does not absorb water. Easy to handle and place. The outer lip peels back with ease to open and start onto a conductor from either end. With a push at the other end, the full length slides on as the lips zip closed around the conductor. To remove each piece, open one end and strip the remainder off the conductor.

## Product Details

### General

Color	Orange
Style	Straight on both ends
Type	III
UPC	096359020738

### Dimensions

Diameter	1.25 in
Length	36 in
Weight	2.617 lb

### Electrical Ratings

Voltage Rating	Class 2 V
----------------	-----------

### Logistics

Pallet Quantity	180 EA
-----------------	--------

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)