



Class 3, Short-Lip Flexible Line Hose, 3'

by CHANCE Utility
Catalog ID: C4060297

LINE HOSE, 1-1/2"X36" STRAIGHT, Much lighter in weight than other flexible dielectric cover-up, Chance Line Hose helps protect workers from accidental contact with conductors. In accordance with ASTM D 1050-90, Chance ozone/corona resistant thermoplastic elastomer offers excellent performance properties. It does not absorb water. Easy to handle and place. The outer lip peels back with ease to open and start onto a conductor from either end. With a push at the other end, the full length slides on as the lips zip closed around the conductor. To remove each piece, open one end and strip the remainder off the conductor.



* Representative image

Product Details

General

Color	Orange
Style	Straight on both ends
Type	III
UPC	096359020769

Dimensions

Diameter	1.5 in
Length	36 in
Weight	5.88 lb

Electrical Ratings

Voltage Rating	Class 3 V
----------------	-----------

Logistics

Pallet Quantity	126 EA
-----------------	--------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com