



* Representative image

Ground Clamp - Duckbill - Mounted 6' II-B-5

by CHANCE Utility
Catalog ID: C6000198

GROUND CLAMP- DUCKBILL - MTD 6FT -II-B-5, Duckbill Grounding Clamp with eye screw, serrated jaw, ASTM Grade 5H, 1.506" Jaw Opening. Continuous Current Amps (400), Fault Current - 15 Cycles (43,000), Fault Current - 30 Cycles (30,000), Recommended Torque (250 in.-lb.), Main Line Range - Max (700kcmI ACSR (1.293")), Main Line Range - Max (#6 Sol. Cu. 0.162"), Jumper Range - Max (4/0 Grd. Cable).

Product Details

General

Bolt Installation Torque (Recommended)	20 ft-lbs
Handle Type	Hotstick
Jaw Type	Serrated Jaws
Material	Aluminum
Terminal Connection Type	5/8"-11 Thread
UPC	096359023333

Dimensions

Jaw Opening Size - Maximum	1.506 in
Jaw Opening Size - Minimum	.162 in
Length	6 in
Weight	9.8 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Threaded Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Threaded Terminal

Certifications and Compliance

Fault Current - ASTM Grade	ASTM Grade 5
----------------------------	--------------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com