



* Representative image

Jumper Set - 15kV Large Clamp

by CHANCE Utility
Catalog ID: C6010174

15kV, 12' of 4/0 cable, insulated large jumper clamp, main line range of 0.162" to 0.883"

- 15kV large clamp has 7-1/2" handle below handguard
- Insulated clamp handles allow for application with appropriately-rated Rubber Gloves
- Meets ASTM F2321 Standard Specification
- For bypassing work areas when equipment is under repair
- For upgrading lines and making temporary or emergency repairs
- Pre-assembled for popular distribution-system voltages, 10 sets offer a choice of cable sizes
- Continuous-current ratings for sets range from 200 to 400 amperes based on cable size selected
- AWG size and voltage rating are embossed at 4' intervals on EPR (ethylene-propylene) insulated jacket
- Insulation and conductor screen meet and exceed ICEA-NEMA standard S-68-516
- Extra-flexible conductors are alloy-coated copper-stranded rope per ASTM B-189 or B-33

Product Details

General

Style	Rubber Glove Applied
UPC	096359024620

Dimensions

Length - Jumper	144 in
Weight	22.54 lb

Electrical Ratings

Current Rating	400 A
Voltage Rating	15 kV

Conductor Related

Conductor Diameter (Main) - Maximum	0.88 in
Conductor Diameter (Main) - Minimum	0.162 in
Conductor Size	4/0 AWG

Logistics

Pallet Quantity	20 EA
-----------------	-------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com