



15 kV, 110 kV BIL, Type C Standard Porcelain Cutout w/300A Solid Blade

by CHANCE Utility
Catalog ID: C710133E

15 kV, 110 kV BIL, Standard Type C Porcelain Cutout with a 300A solid blade, small eyebolt connector and no bracket.

* Representative image

Product Details

General

Bracket Type	No Bracket
Description - Replacement Fuse Holder	T710-133T
Type	Cutout
UPC	096359029298

Dimensions

Weight	16.66 lb
--------	----------

Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	8.7" (220mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	38° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

Logistics

Pallet Quantity	72 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com