



15 kV, 110 kV BIL, Type C Standard Porcelain Cutout w/200A 12kAIC fuseholder

by CHANCE Utility
Catalog ID: C710143PB

15 kV, 110 kV BIL, Standard Type C Porcelain Cutout with a 200A, 12kAIC fuseholder, parallel-groove connector and a NEMA "B" crossarm bracket.

* Representative image

Product Details

General

| | |
|---------------------------------------|----------------------------------|
| Bracket Type | NEMA "B" Heavy Duty for crossarm |
| Description - Replacement Fuse Holder | T710-143T |
| Type | Cutout |
| UPC | 096359240099 |

Dimensions

| | |
|--------|-----------|
| Weight | 18.708 lb |
|--------|-----------|

Electrical Ratings

| | |
|-----------------------------------|--|
| BIL | 110 kV |
| Creep and Leakage Distance | 8.7" (220mm) |
| Current Rating | 200 A |
| Fuselink Current Range | 140A to 200A - removable buttonhead fuse link only |
| Reference Voltage Limit - Minimum | Thru 14.4kV |
| Temperature Rise - Max. at 300A | 38° C |
| Voltage - Maximum | 15 kV |
| Voltage - Radio Interference | Ambient @ 9.41kV |
| Voltage Rating | 15 kV |

Logistics

| | |
|------------------|-------|
| Pallet Quantity | 72 EA |
| Standard Package | 1 |

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com