



27 kV, 125 kV BIL, Type C Standard Porcelain Cutout w/300A Solid Blade

by CHANCE Utility
Catalog ID: C710233L

27 kV, 125 kV BIL, Standard Type C Porcelain Cutout with a 300A solid blade, large eyebolt connector and no bracket.

* Representative image

Product Details

General

Bracket Type	No Bracket
Description - Replacement Fuse Holder	T710-233T
Type	Cutout
UPC	096359029779

Dimensions

Weight	18.434 lb
--------	-----------

Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	300 A
Reference Voltage Limit - Minimum	Thru 24.9kV
Temperature Rise - Max. at 300A	33° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @15.66kV
Voltage Rating	27 kV
Withstand Current - Short Time (10 cycles)	12,000 Amps Asym.

Logistics

Pallet Quantity	48 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com