



* Representative image

27 kV, 150 kV BIL, Type C Standard Porcelain Cutout w/200A 10kAIC fuseholder

by CHANCE Utility
Catalog ID: C710342PB

27 kV, 150 kV BIL, Standard Type C Porcelain Cutout with a 200A, 10kAIC fuseholder, parallel-groove connector and a NEMA "B" crossarm bracket.

Product Details

General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Corrosion Resistant?	No
Description - Replacement Fuse Holder	T710-342T
Type	Cutout
UPC	096359239888

Dimensions

Weight	20.247 lb
--------	-----------

Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	200 A
Fuselink Current Range	140A to 200A
Reference Voltage Limit - Minimum	No Restrictions thru 24.9kV; *26.4 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Maximum	27 kV
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	27 kV

Logistics

Pallet Quantity	42 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems

210 N. Allen Centralia, MO 65240 USA

Phone: (573) 682-5521

Fax: (573) 682-8475

Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521

Fax: +1-573-682-8516

Email: hpsintlcs@hubbell.com