



15 kV, 110 kV BIL, Type C Linkbreak Porcelain Cutout w/100A 10kAIC fuseholder

by CHANCE Utility
Catalog ID: C720112LB

15 kV, 110 kV BIL, Linkbreak Type C Porcelain Cutout with a 100A, 10kAIC fuseholder, large eyebolt connector and a NEMA "B" crossarm bracket.

* Representative image

Product Details

General

| | |
|---------------------------------------|----------------------------------|
| Bracket Type | NEMA "B" Heavy Duty for crossarm |
| Description - Replacement Fuse Holder | T720-112T |
| Type | Cutout |
| UPC | 096359030485 |

Dimensions

| | |
|--------|-----------|
| Weight | 19.345 lb |
|--------|-----------|

Electrical Ratings

| | |
|-----------------------------------|------------------|
| BIL | 110 kV |
| Creep and Leakage Distance | 8.7" (220mm) |
| Current Rating | 100 A |
| Fuselink Current Range | 1A to 100A |
| Reference Voltage Limit - Minimum | Thru 14.4kV |
| Temperature Rise - Max. at 300A | 38° C |
| Voltage - Maximum | 15 kV |
| Voltage - Radio Interference | Ambient @ 9.41kV |
| Voltage Rating | 15 kV |

Logistics

| | |
|------------------|-------|
| Pallet Quantity | 72 EA |
| Standard Package | 1 |

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com