



15/27 kV, 125 kV BIL, Type C Linkbreak Porcelain Cutout w/100A 12kAIC fuseholder

by CHANCE Utility
Catalog ID: C720213PB

15/27 kV, 125 kV BIL, Linkbreak Type C Porcelain Cutout with a 100A, 12kAIC fuseholder, parallel-groove connector and a NEMA "B" crossarm bracket.

* Representative image

Product Details

General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Description - Replacement Fuse Holder	T720-213T
Type	Cutout
UPC	096359030591

Dimensions

Weight	21.099 lb
--------	-----------

Electrical Ratings

BIL	125 kV
Creep and Leakage Distance	12.6" (319mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 14.9kV; *20.8 thru 24.9kV
Temperature Rise - Max. at 300A	33° C
Voltage - Radio Interference	Ambient @15.66kV
Voltage Rating	15/27 kV

Logistics

Pallet Quantity	48 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com